



PCB LAYOUT(TOP VIEW)
(T=1.60mm)

备注:

1) 材质:

- 1-1 本体:LCP 94V-0 黑色
- 1-2 端子:C2680
- 1-3 外壳:C2680或SPCC

2) 镀层:

2-1 端子:所有面镀镍, 触点镀金(镀金G/F u”+50u”锡MIN), 焊脚镀锡50u”MIN,

3) 技术规格

- 3-1. 额定电压:40V
- 3-2. 额定电流:0.5A
- 3-3. 绝缘电阻:100兆欧最小
- 3-4. 接触电阻:30毫欧最大
- 3-5. 操作温度:-20度到85度
- 3-6. 插入力:44.1N Max
- 3-7. 拔出力:9.8~44.1N;
- 3-8. 耐久:10000次

4	STOPPLE	1	LCP	UL94V-0,BL
3	SHELL	1	C2680R&SPCC	PLATED NI
2	HOUSING	1	LCP	UL94V-0,BL
1	CONTACT	21	C2680R-H	PLATED Au
NO.	ITEM	Q'TY	DESCRIPTION	FINISH

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: HDMI A/F 13H CONN
			PAR HDMI-210L
			DWN
			CHKD
DECIMALS:	ANGLES:	APVD	
X.X:±0.25	X.°:±1.5'	SCALE 1:1 UNIT:MM	
X.XX:±0.15	X.X:±1.0'	SIZE:A4	
X.XXX:±0.10		CUSTOMER COPY	SHEET:1F1 REV:A