




SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: PA66 UL94-V0



Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XHD-2Y	2.50	5.25
3	HC-XHD-3Y	5.00	7.75
4	HC-XHD-4Y	7.50	10.25
5	HC-XHD-5Y	10.00	12.75
6	HC-XHD-6Y	12.50	15.25
7	HC-XHD-7Y	15.00	17.75
8	HC-XHD-8Y	17.50	20.25
9	HC-XHD-9Y	20.00	22.75
10	HC-XHD-10Y	22.50	25.25
11	HC-XHD-11Y	25.00	27.75
12	HC-XHD-12Y	27.50	30.25

			GENERAL TOLERANCE		制图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	2.50 孔座	版本 REV.	A
1			初版发行		比例 SCALE		产品料号 PART NO.	HC-XHD-NY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1