



- NOTES:**
SPECIFICATION 规格:
 1. CURRENT RATING 额定电流: 3.0A MAX
 2. VOLTAGE 电压: 100 VAC
 3. TEMPERATURE RANGE 工作温度: -30 °C ~ 85 °C
 4. CONTACT RESISTANCE 接触电阻: 40 MILLIONHM MAX
 5. INSULATION RESISTANCE 绝缘电阻: 100 MEGOHMS MIN.
 6. LNSERTION FORCE 插入力: 5N~20N
 7. UNMATING FORCE 拔出力: 8N~20N
 8. DURABILITY 工作寿命: 10,000 CYCLES

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
5	COVER	HIGH TEMPERATURE PLASTIC	LCP BLACK	1PCS
4	SPRING	STAINLESS STEEL	---	2PCS
3	LATCH	STAINLESS STEEL	TIN:90-120u"Min/Ni base:50u"Min Plated	1PCS
2	SHELL	STAINLESS STEEL	Ni:50u"Min Plated	1PCS
1	TERMINAL HOUSING	HIGH TEMPERATURE PLASTIC	LCP BLACK/CONTACT:AU:1u"Min Ni base50u"Min	2PCS

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

U263-24XN-4BQC13

- 1:AU 1U"
- 2:AU 3U"
- 5:AU 15U"
- 6:AU 30U"

RECOMMENDED PCB LAYOUT($\pm 0.80 \pm 0.05$)
 COMPONENT SIDE(GENERAL TOLERANCE: ± 0.05)

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES



DSND		SCALE: N/A	MODEL TYPE: Type-C 3.1
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	DWG NO.: U263-24XN-4BQC13
APPD		SIZE: A4	WEIGHT
			SHEET 1/1
			REVISIOI A0

XKB INDUSTRIAL PRECISION CO.,LIMITED