



- Notes:
- Materials:
Contacts: Phosphor Bronze,
Insulator: LCP or PA6T
Shell: cold Roller Steel or brass, Nickel Plated.
 - Electrical:
Contact Current Rating : 1Amp, 30V AC
Dielectric Withstanding Volt: AC 500V/Min. R.M.S.
Insulation Resistance: 1000M Ohm Min. at 250V DC
Contact Resistance: 30Miliohms Max.
Operating Temperature: -55°C to +85°C
 - Mechanical:
Mating Force: 3.57Kg. Max.
Unmating Force: 1.02Kg. Min.

Ordering Information

HC-B-003 - 4P - * * * - *A - * - 15

Pin	Type	Current	Colour
4P	TM=Top Mount (RE.L)	(RE.RO)	Black
6P	MM=Mid Mount (RE.RO)	Rated	White
9P	VS=Vertical SMT (RE.RO)	1A	Blue
2xNP	DIP=DIP (RE.RO)	1.5A	Green
		3A	Orange
			Purple
			Yellow

		GENREL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 Shenzhenuacantianlu ELECTRONICS CO., LTD			
		DIM	TOL	审核 CHECK					
		X.X	±0.30	批准 APPROVAL		产品名称 TITLE	USB 2.0 BF 4P 板上	版本 REV.	A
1		X.XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-B-002-4P-TM16.0-1A-X-15	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection	材料 MATERIAL		页次 SHEET	1/1