


PCB HOLES(THE PATTERN SIDE) t=1.6mm  
NOTE:GENERAL TOLERANCE:±0.1mm



电气特性:Electrical:

- 额定电流: Current Rating  
1.5A/contact terminal
- 额定电压: Voltage Rating  
30V DC
- 接触阻抗: Contact Resistance  
30 milliohms MAX
- 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
- 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

物理性能:Mechanical:

- 插拔力: Connector Mate and Unmate Force  
Mate force:3.57kgf (MAX)  
Unmate force:1.02kgf (MIN)
- 端子保持力: Terminal Retention  
1.2kgf (MIN)
- 寿命: 1500次
- 原材料:Material:  
1. 塑胶:Housing:LCP BK  
2. 端子:Contact:Copper Alloy C2680  
3. 外壳:Shell:C2680  
电镀:Finish:  
1. 端子Contact: Au 0.7u" Plated on contact area  
Tin50u" Plated on solder area  
Nickel 50u" Plated underplating over all.  
2. 外壳Shell: Nickel 50u"Min plating over all.

# 深圳市精拓金电子有限公司

## 产品图

PRODUCT CHART DWG

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

### 公差一览表

TOLERANCE UNLESS OTHERWISE	公差
X	±0.25
.X	±0.20
.XX	±0.15
.XXX	±0.10

单位 UNITS	MM
比例 SCALE	1:1
日期 DATE	2015/10/20
制图 DRAWING	林属升
审核 CHKD	郭志富
核准 APPD	黄国荣
产品料号 PRODUCT PART NO.	909-262A2025D10100
产品名称 PRODUCT NAME	AF10.0B戴后两脚无边喇叭CP黑胶7.80IP无耳朵
角法	版本 A0