



PCB LAYOUT

目录 MAPX	设置内容 MODIFICATION	日期 DATE
------------	----------------------	------------

电气特性:Electrical:

- 1.额定电流 : Current Rating
1.5A/contact terminal
- 2.额定电压 : Voltage Rating
30V DC

- 3.接触阻抗:Contact Resistance
30 milliohms MAX

- 4.耐电压:Dielectric Withstanding Voltage:
500 V AC AT Sea Level

- 5.绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力 : Connector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Umate force:0.7kgf(MIN)

- 2.端子保持力 : Terminal Retention
1.2kgf(MIN)

- 3.寿命 : 1500次

原材料:Material:

- 1.塑胶:Housing: LCP NC
 - 2.端子:Contact:Copper Alloy C2680
 - 3.外壳:Shell:C2680
- 电镀:Finish:

- 1 端子Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
- 2 外壳Shell: Nickel 50u" Min plating over all.

产品图

PRODUCT CHART DIMS

Pin NUMBER	SIGNAL NAME
------------	-------------

1	V BUS
2	D-
3	D+
4	GND

公差一览表
TOLERANCE UNLESS OTHERWISE

X	±0.25	X	±5°
.X	±0.20	X	±2°
.XX	±0.15	.XX	±1°
.XXX	±0.10	.XXX	±0.5°

深圳市精拓金电子有限公司

单位 UNITS	MM	制图 DRAWING	林属升	产品料号 PRODUCT PART NO.	904-232B2031S10100
比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	AF鱼叉脚贴板有边内弹铜壳反向 LCT本色1.0挂
日期 DATE	2015/10/20	核准 APRD	黄园荣	角法 NEW	版本 VER
					A0