

目錄 MAPX	設變內容 MODIFICATION	日期 DATE

电气特性:Electrical:

- 1.额定电流 : Current Rating
1.5A/contact terminal
- 2.额定电压 : Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
30 milliohms MAX
- 4.耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Level
- 5.绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:





- 1.插拔力 : Cnnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:0.7kgf(MIN)
- 2.端子保持力 : Terminal Retenion
1.2kgf(MIN)
- 3.寿命: 1500 次

原材料:Matorial:

- 1.塑胶:Housing: LCP BK
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell:SPCC

电镀:Finish:

- 1 端子Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
- 2 外壳Shell: Nickel 50u"Min plating over all.



PCB:LAYOUT

深圳市精拓金电子有限公司

Pin NUMBER		SIGNAL NAME		产品图 PRODUCT CHART DWG		单位 UNITS					
1	2	3	4	公差一览表 TOLERANCE UNLESS OTHERWISE		MM	制图 DRAWING	林属升	产品料号 PRODUCT PART NO.	904-241A2022S10100	
1	VBUS	X.	±0.25	X'	±5'	比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	AF鱼叉脚贴板无边内弹铁壳LCP黑胶1.2柱
2	D-	.X	±0.20	.X'	±2'	日期 DATE	2015/10/20	核准 APPD	黄国荣	角法 VIEW	版本 VER
3	D+	.XX	±0.15	.XX'	±1'						A0
4	GND	.XXX	±0.10	.XXX'	±0.5'						