

目録 MAPX	按变内容 MODIFICATION	日期 DATE
------------	----------------------	------------

电气特性:Electrical:

- 1.额定电流 : Current Rating
1.5A/contact terminal
- 2.额定电压 : Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
30 milliohms MAX
- 4.耐电压:Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 5.绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN




物理性能:Mechanical:

- 1.插拔力 : Connector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Umate force:0.7kgf(MIN)
- 2.端子保持力 : Terminal Retention
1.2kgf(MIN)
- 3.寿命: 1500 次

原材料:Material:

- 1.塑胶:Housing: LCP NC
 - 2.端子>Contact:Copper Alloy C2680
 - 3.外壳:Shell:SPCC
- 电镀:Finish:

- 1 端子Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
- 2 外壳Shell: Nickel 50u"Min plating over all.



PCB LAYOUT

产品图 PRODUCT CHART DWG		单位 UNITS		制图 DRAWING		产品料号 PRODUCT PART NO.	
公差一览表 TOLERANCE UNLESS OTHERWISE		MM		林属升		904-241A2031S10100	
Pin NUMBER	SIGNAL NAME	X	±0.25	X'	±5'	AF鱼叉脚贴片无边内弹壳壳LCP本色1.0挂	
1	VBUS	X	±0.20	X'	±2'	版本 VER	
2	D-	.XX	±0.15	.XX'	±1'	A0	
3	D+	.XXX	±0.10	.XXX'	±0.5'		
4	GND						

深圳市精拓金电子有限公司