

目錄 MAPX	設變內容 MODIFICATION	日期 DATE
------------	----------------------	------------

电气特性:Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voitage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Lnsulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:



1. 插拔力: Cnector Mate and Unmate Force  
Mate force: 3.57kgf (MAX)  
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retenion  
1.2kgf (MIN)
3. 寿命: 1500次

原材料: Material:

1. 塑胶: Housing: PBT BK
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: SPCC

电镀: Finish:

1. 端子 Contact: Au 0.7u" Plated on contact area  
Tin50u" Plated on solder area  
Nickel 50u" Plated underplating over all.
2. 外壳 Shell: Nickel 50u" Min plating over all.



# 深圳市精拓金电子有限公司

Pin NUMBER		SIGNAL NAME		产品图 PRODUCT CHART DWG		单位 UNITS		MM	制图 DRAWING	林属升	产品料号 PRODUCT PART NO.	917-181A102ES60200				
1		VBUS		公差一览表 TOLERANCE UNLESS OTHERWISE		比例 SCALE	1:1	审核 CHKD	郭志富	核准 APPD	黄国荣	产品名称 PRODUCT NO.				
2		D-		X.	±0.25							X'	±5'	角法 VIEW	版本 VER	A0
3		D+		.X	±0.20							.X'	±2'	AM/SMT弯脚铁壳壳带柱PBT黑胶 (YLD)		
4		GND		.XX	±0.15							.XX'	±1'			
				.XXX	±0.10	.XXX'	±0.5'									