


MAPX	MODIFICATION	DRW	DATE

NOTES:

1. MATERIAL: SEE "TABLE 1";
2. FINISH: SEE "TABLE 1";
3. ELECTRICAL :
 - 3-1. CONTACT CURRENT RATING :
3A (VBUS PIN 1.5A/PIN MAX),
3A (GND PIN 1.25A/PIN MAX), 0.25A/PIN
(OTHER PIN).
 - 3-2. INSULATION RESISTANCE :
100 MEGAOHMS MIN. AT 250VDC.
 - 3-3. DIELECTRIC WITHSTANDING VOLTAGE :
100VAC MIN.
 - 3-4. LOW LEVEL CONTACT RESISTANCE :
INITIAL 40mΩ MAX.
AFTER 50mΩ MAX.
4. MECHANICAL CHARACTERISTICS :
 - 4-1. MATING FORCE: 5~20N ;
 - 4-2. UNMATING FORCE: 6~20N (INITIAL),
6~20N (AFTER 10000 CYCLES) ;
 - 4-3. DURABILITY : 10,000 MATING CYCLES.
 - 4-4. OPERATING TEMPERATURE : -40° C TO +80° C

TABLE 1:

NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK
①	She11	1	SUS 304	NI PLATING:	~=0.30mm
②	MD PLATE	1	SUS 304	Au:1μ	~=0.15mm
③	Terminal	16	C2800		
④	Housing	3	L27 1301		



产品图
PRODUCT CHART DWG

公差一览表	公差	公差	公差
TOLERANCE UNLESS OTHERWISE	±0.25	X	±5.°
	±0.20	X	±2.°
	±0.15	XX	±1.°
	±0.10	XXX	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位	MM	制图	林属升	制图料号	918-418K2023S40023
比例	1:1	审核	郭治富	产品名称	TYPE-03, 1通道, 上7, 35V耐本贴
SCALE		OKD	黄国荣	PRODUCT NO.	带铜片半封装SMT有注, 16PIN/2A
日期	2020-05-22	APPD		角法	
DATE				版本	A0
				VER	