




1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A: (AWG32-AWG28)
Circuit: R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	10
2	黑色	9
3	黄色	8
4	白色	7
5	绿色	6
6	蓝色	5
7	紫色	4
8	灰色	3
9	棕色	2
10	橙色	1

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X9821HM-10A-N0HF	2PCS		
2	X9821TF-PSN	20PCS		
3	UL1571/28AWG. 红.黑.黄.白. 绿.蓝.紫.灰. 棕.橙色	各1PCS	300MM	
总量				

					ANGLAR	±5°	XKLB	DSND	SCALE: N/A	DRAWING NO.		
					L ≤ 4	±0.2		DWN	VIEW:	X9821TF-PSN-A28RBYWGLPEN(YR)-L300-X9821TF-F		
					4 < L ≤ 16	±0.3		CHKD	UNIT: mm/in	PART NO.:		
					16 < L ≤ 63	±0.4		APPD	SIZE: A4	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	UNSPECIFIED TOLERANCES			WEIGHT	SHEET	REVISION
REVISIONS							XKB INDUSTRIAL PRECISION CO., LIMITED				1/1	A0
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn												