




REV.	RELEASE AND CHANGE SUMMARY	DATE
A	首次发行	2022.12.15



技术要求:

- 1 材质与表面处理: 详见BOM表。
- 2 电气特性: 特性阻抗:50Ω; 工作频段:DC ~ 6GHz; 电压驻波比:最大1.50。
- 3 外观检验: 目视全检。制品形制规整, 无变形、划伤、破损、脏污、异色等不良。
- 4 尺寸检验: [♦],FAI首件工艺检验项目; [◆],QIP重点检验项目; [★],CPK制程管制项目。
- 5 盐水喷雾试验: 抽样检验, 无外观不良。
试验条件: 使用盐水喷雾试验机, 盐水浓度5%±1%, 温度35℃±2℃, 连续试验24小时, 试验后清洁表面沉积物, 常温状态放置2小时后检验。
- 6 环保要求: 制品及其生产制程中所有使用到的物料均需满足欧盟RoHS指令要求。

3	2LC15SF044	母针: 黄铜,镀金	1
2		绝缘体: PTFE,白色	1
1		主体: 黄铜,镀金	1
No.	PART NUMBER	PART NAME AND DESCRIPTION	Q'TY
BOM 物料清单			

GENERAL TOLERANCE: UNLESS OTHERWISE SPECIFIED LINEAR: 0.5 < L ≤ 6 ± 0.05 6 < L ≤ 30 ± 0.10 30 < L ≤ 120 ± 0.20 ANGULAR: 0 < L ≤ 10 ± 1°30' 10 < L ≤ 50 ± 1°00' 50 < L ≤ 120 ± 0°30'		FILE TYPE: 零件图	Dongguan HUANGJIE Communication Technology Co., Ltd. 东莞市皇捷通讯科技有限公司		
DRA./DATE: S.He 22.12.15		CHE./DATE:	TITLE: 180度SMA母头母针,SQ6.50*13.50mm, 夹板间距1.70mm,FOR PCB		
APP./DATE:		CODE: 2LC15SF044			
FILE FORM: HJ-QR-E-03 22.09.01	SIZE: A4	UNIT: mm	PRO.: 3rd	SCALE: 4:1	PAGE: 1/1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO HUANGJIE AND SHOULDN'T BE USED WITHOUT WRITTEN PERMISSION.

