





ROHS



- 1.Pin pitch: 1.27MM
- 2.Voltage rating : 300V AC
Current rating : 1mps
- 3.Insulation resistance: $\geq 500M\Omega$
- 4.Operating temperature: $-40^{\circ}C \sim +105^{\circ}C$



②	PIN	—	—	Phosphor bronze	Au Plated	—
①	Base	—	1	NYLON-6T	Natural	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	 ELECTRONICS CO.,LTD		
DRAWN	LIUCAN	2022.3.9				
CHECKED			TITLE:			
APPROVALS				PART NO.	PH1.27WV-2*□P	
TOLERANCES ARE	30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	± 0.20				
	5~10	± 0.15	$\pm 2'$	DRAWING NO.		SHEET 1 OF 1
	~ 5	± 0.10				

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.