


1.SPECIFICATIONS  
 INSULATION RESISTANCE: 500M min.AT DC 500V DC  
 WITHSTANDING VOLTAGE: 250V ACrms FOR 1 MINUTE  
 CONTACT RESISTANCE: 100M max. AT 10MA/20mV max  
 CURRENT RATING: 0.5A  
 VOLTAGE RATING: 5.0 vrms  
 OPERATING TEMP.RANGE:-55 C+85 C  
 MATING CYCLES: 5000 INSERTIONS


2.MATERIAL:  
 INSULATOR: H-TEMPERATURE PLASTIC,UL 94V-0,  
 COLOR:BLACK  
 TERMINAL: COPPER ALLOY,T=0.15mm  
 SHELL: STAINLESS STEEL,T=0.15mm

3.FINISH:  
 TERMINAL:50u" min NICKEL UNDERPLATED ON ALLOVER,GOLD PLATING  
 ON CONTACT ARER, FLASH GOLD ON SOLDER TAIL.  
 SHELL:50u" NICKEL UNDERPLATED ON ALLOVER, GOLD FLASH ON SOLDER  
 LATCH



RECOMMENDED PCB LAYOUT

CIRCUIT:



SIM pin assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved

兆星精密电子(深圳)有限公司

DIMENSIONS INIT: mm  
 UNLESS OTHERWISE SPECIFIABLE  
 DIMENSION TOLERANCE  
 X.X: ± 0.25  
 X.XX: ± 0.10  
 X.XXX: ± 0.05  
 ANGULAR: ± 1°

PRODUCT NAME : 自弹式 MiniSIM卡 卡座 6P	DRAWING:	DATE:
PRODUCT NO. : ZX-SIM-481.85J-6	CHECK:	DATE:
DRAWING NO. :	APPROVED:	DATE:
SCALE: 1:1	DWG ID: P D	REV.: A
		PAGE: 1 of 1

REVISION NO.	ECR NO.	DESCRIPTION	MARK	DATE