

REV.	DESCRIPTION	APPD	DATE

A

B

C

E

F

A




B

C

D


E

F




弹高检测

弹高检测





NOTES:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
- PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: TIN OVER NICKEL.
- MULTIMEDIA CARD COMPATIBLE



RECOMMENDED FPC/FPC DIMENSION



PART NO:		MATERIAL:		 兆星精密电子 (深圳) 有限公司	
LOT NO:		FINSH:			
UNIT: MM	SIZE: A4	COLOR:		TITLE: 0.5mm P数: 24 翻盖式 双侧触点/上下接	
TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15		GENERAL ANGLE: X.X=±3.0° X.XX=±2.0°		DR:	DWG NO: ZX-FPC-FWSX0.5PH224
				CHK:	SCALE: 1:1
				APP:	SHEET: 1 OF 1