







1 2 3 4 5 6 7 8 9

F  
E  
D  
C  
B  
A



Specifications  
 Current Rating:3Amp  
 Voltage Rsting:250V AC/DC  
 Temperature Range:-25°C to +85°C  
 Contact Resistance:10mΩ Max.  
 Insulation Resistance:1000MΩ Min.  
 Withstanding Volatge:1000V AC/minute  
 Materials  
 Contact Material:PA66  
 All materials must meet GREENCONN  
 hazardous substances control standards.



**Ordering Information**

GFG041 - XX A XX

No. of Pins  
02-16

Materials /Color  
P1=NY 66/White

Pins	DIMENSIONS	
	L	M
02	7.30	2.5
03	9.80	5.0
04	12.30	7.5
05	14.80	10.0
06	17.30	12.5
07	19.80	15.0
08	22.30	17.5
09	24.80	20.0
10	27.30	22.5
11	29.80	25.0
12	32.30	27.5
13	34.80	30.0
14	37.30	32.5
15	39.80	35.0
16	42.30	37.5

格稜股份有限公司  
**Greenconn Corporation**

REV. A UNIT. mm SCALE. 1:1 PAGE. 1/1

GENERAL TOLERANCE	
X:±	X.±
.X'±	.X±0.25
.XX'±	.XX±0.15
.XXX'±	.XXX±0.10

DESIGNED: DATE:  
 CHECKED: DATE:  
 APPROVED: DATE:

DWG. NO.  
GFG041-HA  
 PART NO.  
GFG041-XX A XX

TITLE.  
2.5mm pitch housing

1 2 3 4 5 6 7 8 9