



- 注：
1. 標示"Ⓧ"為全尺寸測量部位。
 2. 標示"Ⓜ"為首件與尾件測量部位。
 3. 標示"▽"為首件、尾件與巡檢測量部位。
 4. 所有材料必須滿足GREENCONN有客物質管控標準。

Ordering Information

GRR128 - 01 XX XX
 Standard Plating
 01-Tin
 Material
 AB-Phosphor Bronze

Wire range	Insulation O.D	Materials	Finish	Qty./reel	DATE:	DWG. NO.	TITLE:
AWG#22~28	1.5 mm (max)	Phosphor Bronze	Tin-Plated	10000pcs	DATE:	GRR128-T1	2.0 Pitch Terminal
格 稜 股 份 有 限 公 司 Greenconn Corporation							
REV. 01	UNIT. mm	SCALE. 1:1	PAGE. 1/1	DESIGNED:	CHECKED:	DATE:	PART NO.
				XXX±/	XXX±/	DATE:	GRR128-01XXXX
				XXX±/	XXX±/	DATE:	
				XXX±/	XXX±/	DATE:	
				XXX±/	XXX±/	DATE:	