




Recommended P.C.B Layout (Top Side)  
(PCB BOARD TOLERANCE ±0.05)




SPECIFICATIONS

Rated Current: 1.0AMP  
Contact Resistance: 20mΩ Max  
Withstand Voltage: 500V AC/DC  
Insulation Resistance: 1000MΩ Min  
Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze  
Contact Plating: Au Over Ni  
Insulator Material: Polyester (UL94V-0)  
Standard: PA6T  
Max. Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

Ordering Information



			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	1.27双排 排母 贴片	版本 REV.	A
			X. XX	±0.20	比 例 SCALE		产品料号 PART NO.	PM127-2-N-S-4.3-XX	单 位 UNITS	mm
			X. XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°							