



SPECIFICATIONS
 Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Copper Alloy
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 260°C±5°C 5S

Ordering Information

PM 254 - * - N - WS - * - **

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type Z=直插 S=贴片 W=弯插	Length (Plastic) (mm)	Contact Plating G0:Gold Flash G1:10μ Gold G2:30μ Gold G3:50μ Gold G4:100μ Gold G5:150μ Gold G6:300μ Gold S0:Gold Flash/Tin S1:Tin
---	------------------------	------------------------------	--------------------------	--

			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	2.54双排 排母 卧贴(塑高8.5)	版本 REV.	A
			X. XX	±0.20	比 例 SCALE		产品料号 PART NO.	PM254-2-N-WS-8.5-XX(L16.9)	单 位 UNITS	mm
			X. XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle	±3.0°						
1	初版发行									
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								