


| linear dimension(Tolerances Standard GB/T 14486-2008) | | | | | | | | — | ∇ | \perp |
|---|-------|--------------|---------------|---------------|----------------|-----------------|-------------|-------|----------------|-------------|
| variable range | to 6 | over 6 to 10 | over 10 to 30 | over 30 to 60 | over 60 to 100 | over 100 to 160 | over 160 to | to 10 | over 10 to 100 | over 100 to |
| tolerance | ±0.20 | ±0.30 | ±0.50 | ±0.70 | ±1.00 | ±1.30 | ±1.60 | 0.10 | 0.30 | 0.60 |



| UL/CUL 技术参数 | UL/CUL Technical Data | | | DORABO | | |
|--------------------|------------------------------------|------------------|-----|--------|--|--|
| 等级 | Use Group | B | C | D | | |
| 额定电压 | Rated Voltage [V] | 300 | - | 300 | | |
| 额定电流 | Rated Current [A] | 30 | - | 10 | | |
| 接线范围 | Wire Range | 24-8 | | | | |
| 单/多芯线 | Solid/Stranded [AWG] | | | | | |
| 耐电压 | Withstanding Voltage | 1600V/1Min | | | | |
| IEC 技术参数 | | | | | | |
| IEC Technical Data | | | | | | |
| 过电压类别 | Overvoltage Category | III | III | II | | |
| 污染等级 | Contamination Class | 3 | 2 | 2 | | |
| 额定电压 | Rated Voltage [V] | 400 | 630 | 1000 | | |
| 额定电流 | Rated Current [A] | 32 | 32 | 32 | | |
| 额定冲击电压 | Impulse withstand voltagea [KV] | 6.0 | 6.0 | 6.0 | | |
| 导线截面积 | Conductor cross section | 4.0 | | | | |
| 硬质/柔性导线 | Solid/ flexible [mm ²] | | | | | |
| 材料 | | | | | | |
| 绝缘材料 | Insulation Material | PA66 | | | | |
| 阻燃等级 | Imflammability | UL94V-0 | | | | |
| 导体材料 | Contacto Material | 铜合金 Copper alloy | | | | |
| 导体表面镀层 | Contactive Coating | 镀锡 Ni Plated | | | | |
| 一般参数 | | | | | | |
| 间距 | Pitch [mm] | 7.62 | | | | |
| 极数 | Poles [P] | 2-16 | | | | |
| 剥线长度 | Stripping Length [mm] | 7-8 | | | | |
| 螺丝 | Screw/扭矩 Torque(Max) [N.m] | M3/0.5 | | | | |
| 工作温度 | Operating temperatur [°C] | -40~+105 | | | | |
| 引针尺寸 | Pin Dimensions [mm] | - | | | | |
| PCB板孔径 | PCB Hole Diameter [mm] | - | | | | |

DB3EK — 7.62 — XXP — C — S/P
 (Series No.) (Pitch) (Poles)
 Slottef/Phillips
 (Color) : GN:(Green) , BK:(Black) , BU:(Blue) , RD:(Red) , GY:(Gray)
 OG:(Orange) , WT:(White) , YL:(Yellow) , CR:(Clear)

APPD: JTING Chen 2022.4.6
 CHKD: Duck Mao 2022.4.6
 DRFT: Steven Lu 2022.4.6

DORABO 宁波地博电气有限公司
 Ningbo Dorabo Electric CO., Ltd

NAME: DB3EK-7.62-XXP-C-S

TYPE: CUSTOMER_DRAWING

SIZE: A4

SCALE: 1:1

REV: T0-1

SHEET: 1/1