

| | |
|----------------|-------------|
| PRODUCT NO. | DSHP04TSGER |
| RoHS compliant | |

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:
GOLD FLASH 1u"(min.) SOLDER TAIL,
3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I S G E R

[包装方式: T=管装 R=Reel]






[电键层: B=接触部3u"焊脚部1.2u" G=接触部3u"焊脚部3u" F=接触部10u"焊脚部10u"]

[G=键全金 S=内镀金(接触部)外镀锡(焊脚部)]



[脚型: S脚 / J脚 / 埋脚 / A脚 / 2脚]

[T=低推贴胶 S=低推不贴胶 L=长推]

[产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



| Number | Part Name | Material | Finished |
|--------|------------------|------------------|----------|
| ① | Actuator | UL94 V0 | White |
| ② | Cover | UL94 V0 | Black |
| ③ | Movable | Beryllium Copper | 3u" Gold |
| ④ | Terminal | Brass | 1u" Gold |
| ⑤ | Base | UL94 V0 | Black |
| ⑥ | Terminal Contact | Brass | 3u" Gold |
| ⑦ | Mylar | UL94 V0 | 0.05mm |

| TOLERANCE UNLESS OTHERWISE SPECIFIED | | INSPECTION COPY | |
|--------------------------------------|------------|-----------------|--|
| LINER | ANGLES | PROJECTION | |
| 0 ± 0.25 | 0 ± 2' | | |
| .00 ± 0.15 | .0 ± 1' | | |
| .000 ± 0.10 | .00 ± 0.5' | | |
| DESIGN | kathy | 03/20/12 | |
| DRAWING | | | |
| CHECK | | | |
| APPRO. | | | |

东莞市广智实业有限公司
Dongguan Kingtek Industrial Co., Ltd.

TITLE
BY DSHP SERIES PITCH 1.27mm

PRODUCT FAMILY DSHP SERIES
PRAT NO. DSHP04TSGER

FILE NO. DSHP04TSGER-A
SIZE UNIT SCALE SHEET REV.
A4 mm Z: 1 TOF: 1 A