






Current rating:5A AC/DC
 额定电流:5A AC/DC
 Temperature range:-40°C-+125°C
 温度范围:-40°C-+125°C



K 171894 **W** **R-XX** - **N0** **SN**
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:W-Wafer
- 4.Welding Board Rangle:R-Stright 90°
- 5.Row No.Pin No:XX-09 Pin
- 6.Material:N0-PA66 UL 94V-0
- 7.Palting:SN-Plated Tin



K171894WR-XX-N0SN	PA66	Brass	K171894H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 5.0mm Automobile connector
DWN	VIEW:	PART NO.: K171894WR-XX-N0SN
CHKD	UNIT: mm/in	DWG NO.: X-K171894WR-XX-N0SN
APPD	SIZE: A4	WEIGHT SHEET REVISION



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

ΔX					
ΔX					
ΔX					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	

REVISIONS