


Current rating: 3A AC/DC  
 额定电流: 3A AC/DC  
 Temperature range: -40°C +125°C  
 温度范围: -40°C +125°C

K 174960 W R - XX - PT SN  
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:W-Wafer
- 4.Welding Board Range:R-Stright 90°
- 5.Row No.Pin No:XX-20 Pin
- 6.Material:PT-PBT
- 7.Palting:SN-Plated Tin



K174960WR-XX-PTSN	PBT	Phosphor Bronze	K174960H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE:		
DWN	VIEW:	3.5mm Automobile connector		
CHKD	UNIT: mm/in	PART NO.:		
APPD	SIZE: A4	K174960WR-XX-PTSN		
		DWG NO.:		
		X-K174960WR-XX-PTSN		
		WEIGHT	SHEET	REVISION
			1/1	A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				