

NOTE:



1. 材質:

1-1. 胶芯:PA6T本色(UL94V-0)

1-2. 后盖:PPS本色(UL94V-0)

1-3. 端子:磷铜 C5191R-H


1-4. 固定片:黄铜,C2680R-H




上接触 Up contact

05B20 G XX G XU

- ① Series Name : 05B20 0.5 mm PitchH 2.0mm
- ② Assembly style : L:Low Contact SMT Type U:Upper Contact SMT Type
D:Double-Face Contact SMT Type H:Back-flip Double-Face Contact SMT Type
- ③ Number of terminals :XX 04-67PIN
- ④ Plating : G:Gold Flash Over Nickel T:Tin Over Nickel
- ⑤ Gold-Plated .



RECOMMENDED PCB LAYOUT



RECOMMENDED FFC DIM

NO.OF CKT	DIM=A	DIM=B	DIM=C
4	1.50	7.7	2.60
5	2.00	8.2	3.10
6	2.50	8.7	3.60
7	3.00	9.2	4.10
8	3.50	9.7	4.60
9	4.00	10.2	5.10
10	4.50	10.7	5.60
11	5.00	11.2	6.10
12	5.50	11.7	6.60
13	6.00	12.2	7.10
14	6.50	12.7	7.60
15	7.00	13.2	8.10
16	7.50	13.7	8.60
17	8.00	14.2	9.10
18	8.50	14.7	9.60
19	9.00	15.2	10.10
20	9.50	15.7	10.60
21	10.00	16.2	11.10
22	10.50	16.7	11.60
23	11.00	17.2	12.10
24	11.50	17.7	12.60
25	12.00	18.2	13.10
26	12.50	18.7	13.60
27	13.00	19.2	14.10
28	13.50	19.7	14.60
29	14.00	20.2	15.10
30	14.50	20.7	15.60
31	15.00	21.2	16.10
32	15.50	21.7	16.60
33	16.00	22.2	17.10
34	16.50	22.7	17.60
35	17.00	23.2	18.10
36	17.50	23.7	18.60
37	18.00	24.2	19.10
38	18.50	24.7	19.60
39	19.00	25.2	20.10
40	19.50	25.7	20.60
41	20.00	26.2	21.10
42	20.50	26.7	21.60
43	21.00	27.2	22.10
44	21.50	27.7	22.60
45	22.00	28.2	23.10
46	22.50	28.7	23.60
47	23.00	29.2	24.10
48	23.50	29.7	24.60
49	24.00	30.2	25.10
50	24.50	30.7	25.60
51	25.00	31.2	26.10
52	25.50	31.7	26.60
53	26.00	32.2	27.10
54	26.50	32.7	27.60
55	27.00	33.2	28.10
56	27.50	33.7	28.60
57	28.00	34.2	29.10
58	28.50	34.7	29.60
59	29.00	35.2	30.10
60	29.50	35.7	30.60

ECN BO.		new		2015/5/3		A		Hanyones	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	DATE.		REV.		SCALE: 3:1	
MIKEY	TOM	JERRY	PART NAME	05B20G24G3U		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X	±0.25
			MODEL NAME	05B20G24G3U				X.x	±0.20
			3RD ANGLE PROJ	HANYONES TECH CO.,LTD				X.xx	±0.15
								ANGULAR	±3'
								FILE NO.	