






REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	2020.06.05	Mark



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)



3D视图



SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°C ~ +105°C
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 200° C for30-60seconds
 (220° C for5seconds)

调机时请将5PCS自动送料导针孔堵住,避免消耗挑选工时

3	2BB2032	平口PE袋,L:180mm*W:160mm*T:0.06mm,LDPE/低密度PE	1/1000=0.001
2	2YC018	0.64*L11.4,方针,镀金0.8u"	7
1	2SBKA0103	PA6T PH1*40,P2.54*塑高2.5*W2.5,黑色	7/40=0.2
No.	PART NUMBER	PART NAME & DESCRIPTION	Q'TY

生产统计	
IKG针产品多少PCS产品	
数量:	
日期:	
统计人:	

GENERAL TOLERANCE:	
LINEAR:	
X	±0.30
X.X	±0.20
X.XX	±0.10
X.XXX	±0.05
ANGLE:	
X°	±4.00°
X.X°	±3.00°
X.XX°	±2.00°
X.XXX°	±1.00°

HJ-Tech		东莞市皇捷通讯科技有限公司	
FILE NAME: 零件图	TITLE: 2.54PH 1x7PIN 2.5塑高 180° SIP L11.4 PC3.0 单塑 镀0.8u金 PA6T		
ENG/DATE: Mark/2020.06.05	P/N: 17-1442-002		
APP/DATE:	UNIT: mm	SCALE: 1:1	REVISION: A0
		SHEET: 1/1	

COMPLIANCE WITH THE REQUIREMENT: ■ RoHS; □ HF; □ SONY SS-00259; □ OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE