



Part No	Pin	A	B	C
WAFER-VH3.96-2PWB	2	3.96	9.80	8.60
WAFER-VH3.96-3PWB	3	7.92	13.76	12.56
WAFER-VH3.96-4PWB	4	11.88	17.72	16.52
WAFER-VH3.96-5PWB	5	15.84	21.68	20.48
WAFER-VH3.96-6PWB	6	19.80	25.64	24.44
WAFER-VH3.96-7PWB	7	23.76	29.60	28.40
WAFER-VH3.96-8PWB	8	27.72	33.56	32.36
WAFER-VH3.96-9PWB	9	31.68	37.52	36.32
WAFER-VH3.96-10PWB	10	35.64	45.44	40.28

技术要求:

1. 塑件材料:LCP(UL-94V-0)
2. 接触件:黄铜镀锡
3. 接触电阻:≤30mΩ
4. 绝缘电阻:≥1000MΩ
5. 额定电压:250V AC DC
6. 额定电流:7.0A AC DC
7. 耐压:能承受1000V AC/Minute
8. 工作温度:-25°~+85°
9. 可焊性试验:浸锡面积≥95%温度260, 时间2.5±0.5秒
10. 铅和镉等六大有害物质含量要符合环保要求。

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 压接式(条形)连接器
DECIMALS:	ANGLES:		PAR WAFER-VH3.96-NPWB
.X±0.25	X.°±3'		DWN
.XX±0.12			CHKD
.XXX±0.05		APVD	SCALE:1:1 UNIT:MM
CUSTOMER COPY		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A