






11.36 [0.447]±0.25



- K 202820 T- P SN**
 ① ② ③ ④ ⑤
- ① K:XKBTEK-Car Connector
 - ② XKB Series No.
 - ③ Category : T- Terminal
 - ④ Material:P-Phospor Bronze
 - ⑤ Plating Category: SN-Tin-Plated

K202820T-PSN	Phospor Bronze	Tin-Plated	AWG#22-#28	1.50mm(max)	K202820H
PART NO	Material	Finish(pin)	Wire Range	Insulation O.D.	Suitable XKB Housing

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
DESCRIPTION					DATE	REVISED
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	2.0mm Automobile connector
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	K202820T-PSN
			DWG NO.:
			X-K202820T-PSN
WEIGHT		SHEET	REVISION
		1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED