



Specifications:
 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range:-25℃-+85℃
 温度范围: -25℃-+85℃
 Insulation resistance:100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance:50mΩ Max
 接触电阻: 50mΩ Max

X1254 H - 2xXX A - N0
 ① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-Housing
- 3.Row No.Pin No:2xXX-2x05~2x20 Pin
- 4.Type:A-Double-row connector
- 5.Material:N0-PA66 UL94V-0 (White)

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x05	6.00	9.50	2x13	15.00	19.50
2x06	6.25	10.75	2x14	16.25	20.75
2x07	7.50	12.00	2x15	17.50	22.00
2x08	8.75	13.25	2x16	18.75	23.25
2x09	10.00	14.50	2x17	20.00	24.50
2x10	11.25	15.75	2x18	21.25	25.75
2x11	12.50	17.00	2x19	22.50	27.00
2x12	13.75	18.25	2x20	23.75	28.25

X1254H-2xXXA-N0	PA66	X1254W	X1254T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1254H-2xXXA-N0
CHKD		UNIT: mm/in	DWG NO.: X-X1254H-2xXXA-N0
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				