




剖视图: A-A



剖视图: B-B



剖视图: C-C



剖视图: D-D

Specifications:

规格:

Voltage rating: 50V AC/DC

额定电压: 50V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -25°C~+85°C

温度范围: -25°C~+85°C

Insulation resistance: 100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance: 50mΩ Max

接触电阻: 50mΩ Max

X1254 T - P XX - A
① ② ③ ④ ⑤

1. Series No

2. Category: T-Terminal

3. Material: P-Phosphor

4. Plating: XX: V01-Gold Plated

SN-Tin Plating

5. Type: A Type

X1254T-PXX-A	Phosphor	AWG#32~26	X1254H
PART NO	Material	Wire Range	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1254T-PXX-A
CHKD		UNIT: mm/in	DWG NO.: X-X1254T-PXX-A
APPD		SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
DESCRIPTION					DATE	REVISED
DATE					APPROVED	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						