



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

- a.HOUSING:PP BLACK
- b.SPRING:MUSIC WIRE
- c.TERMINAL:BRASS




(SURFACE PLATING: NI-PLATING)
SEE ORDERING INFORMATION

2.ELECTRIC:

- a.DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL
- b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-AA-B1AJ045-150



3	TERMINAL	8	BRASS	Ni-Plating
2	SPRING	8	MUSIC WIRE, 0.6MM	Ni-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2023-04-03
WEIGHT:		CHKD ZhouRuicai	DATE 2023-04-03
SHEET 1 OF 1		APVD XueShunyong	DATE 2023-04-03
UNIT: mm	SCALE:	SIZE: A4	VIEW:
REV.: A/1	OBJECT: MY	TITLE: 电池盒BH-AA-8J双面靠背 (26#红黑线长150MM剥皮上锡3MM)	
DRAW NO.:WD-CP-0292		PART NO.: BH-AA-B1AJ045-150	