



REV.	ECN NO.	REVISED	DATE

NOTE:



1.MATERIAL:

- a.HOUSING:ABS BLACK UL94V-HB
- b.SPRING:MUSIC WIRE
(SURFACE PLATING: Ni100u"~120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL
- b.OPERATING TEMPERATURE: -10° C~ +100° C



ORDERING INFORMATION

BH-AA-B5BJ038-XX

电池盒

电池型号

SMT TYPE

PLATING:

- A-Au1U"
- J-Ni100U"~120U"
- K-Sn100U"~120U"

MATERIAL:

- 1A-PP BLACK
- 1B-PA66 BLACK
- 2A-PPA BROWN
- 2B-PPA BLACK
- 3A-PPS BROWN
- 3B-PPS BLACK
- 4A-LCP WHITE
- 4B-LCP BLACK
- 5B-ABS BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2022-11-01
		CHKD	ZhouRuicai	DATE	2022-11-01
		APVD	XueShunYong	DATE	2022-11-01
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊕ ⊖
SHEET 1 OF 1		UNIT: mm	REV.: A/1	OBJECT: MY	TITLE: 电池盒BH-AA-B5BJ038-XX (26#定制线长)
		PART NO.:		BH-AA-B5BJ038-XX	
		DRAW NO.:WD-CP-0234			

2	SPRING	6	MUSIC WIRE ϕ 0.55MM	Ni-Plating
1	HOUSING	2	ABS UL94V-HB	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR