




REV.	ECN NO.	REVISED	DATE

NOTE:

- MATERIAL:
 - a. HOUSING: ABS BLACK
 - b. SPRING: MUSIC WIRE
(SURFACE PLATING: Ni100u"~120u")
- ELECTRIC:
 - a. DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL
 - b. OPERATING TEMPERATURE: -10° C ~ +100° C

SEE ORDERING INFORMATION




ORDERING INFORMATION BC-12-B5BJ001-XX

电池盒 ——— PLATING:
 A-Au1U"
 J-Ni100U"~120U"
 K-Sn100U"~120U"

电池型号 ———

SMT 180° TYPE ——— MATERIAL:
 1A-PP BLACK
 1B-PA66 BLACK
 2A-PPA BROWN
 2B-PPA BLACK
 3A-PPS BROWN
 3B-PPS BLACK
 4A-LCP WHITE
 4B-LCP BLACK
 5B-ABS BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2022-04-27
		CHKD	ZhouRuicai	DATE	2022-04-27
		APVD	XueShunyong	DATE	2022-04-27
		WEIGHT:	SCALE:	SIZE: A4	VIEW:
		SHEET 1 OF 1	UNIT: mm	REV.: A/1	OBJECT: MY
		TITLE: 9V电池盒BC-12-1J带盖开关(26#定制 线长剥皮上锡3mm)		PART NO.: BC-12-B5BJ001-XX	
		DRAW NO.:WD-CP-0214			

2	SPRING	2	BRASS	Ni-Plating
1	HOUSING	2	ABS	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR