



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/.	新版发行	20.05.04	Yang
A1.	/.	重新核对图面	21.01.06	LiHui

PIN数	A±0.1	B±0.1	C±0.1
2P	4.30	1.00	3.25
3P	5.30	2.00	4.25
4P	6.30	3.00	5.25
5P	7.30	4.00	6.25
6P	8.30	5.00	7.25
7P	9.30	6.00	8.25
8P	10.30	7.00	9.25
9P	11.30	8.00	10.25
10P	12.30	9.00	11.25

- Specifications:
1. Rated Voltage : 50V AC/DC
  2. Rated Current : 1A AC,DC
  3. Withstand Voltage : 200V AC/minute
  4. Contact Resistance : 50mΩ(MAX.)
  5. Insulation Resistance : 100MΩ(MIN.)
  6. Storage Temperature Range: -40°C~+85°C;
  7. Operation Temperature Range: -25°C~+70°C;

3	插片	黄铜H65	镀镍锡	
2	插针	黄铜H65	镀镍锡	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

**深圳市虹成电子有限公司**

UNLESS OTHERWISE, GENERAL TOLERANCE: X. xxx ±0.05 X. xx ±0.15 X. x ±0.25	NAME: 针座1.0立贴16P编带		P/N: HCZZ0039-16	
	DWG NO:			
THIRD ANGLE PROJECTION 	UNIT:	SCALE:	SIZE:	SHEET:
	MM	1:1	A4	1/1
DRAWN:	CHECKED:		APPROVED:	

ANGULAR:  
X. xx° ±1°  
X. x° ±3°  
X. ° ±5°

RECOMMENDER P.C.B.LAYOUT TOP VIEW  
(COMPONENT SIDE TOLERANCE±0.1)