



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/.	新版发行	20.05.04	Yang
A1.	/.	重新核对图面	21.01.07	LiHui

PIN数	A±0.1	B±0.1	C±0.1
2P	4.30	1.00	3.25
3P	5.30	2.00	4.25
4P	6.30	3.00	5.25
5P	7.30	4.00	6.25
6P	8.30	5.00	7.25

- Specifications:
1. Rated Voltage : 50V AC/DC
  2. Rated Current : 1A AC,DC
  3. Withstand Voltage : 200V AC/minute
  4. Contact Resistance : 50mΩ(MAX.)
  5. Insulation Resistance : 100MΩ(MIN.)
  6. Storage Temperature Range: -40°C~+85°C;
  7. Operation Temperature Range: -25°C~+70°C;

3	插片	黄铜H65	镀镍锡	
2	插针	黄铜H65	镀镍锡	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

**深圳市虹成电子有限公司**

UNLESS OTHERWISE, GENERAL TOLERANCE: X. xxx ±0.05 X. xx ±0.15 X. x ±0.25	NAME:	P/N: HCZZ0039-4	
	针座1.0立贴4P编带		DWG NO:
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°	THIRD ANGLE PROJECTION	UNIT:	SCALE:
		MM	1:1
DRAWN:		SIZE:	SHEET: REV.
		A4	1/1 A1
		CHECKED:	APPROVED:

