





6	7	8
版本	变更内容	工程确认 日期



SPECIFICATIONS

- 1、Current Rating: 9A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 20MΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL99V-0 PIN Brass Tin-plated



PCB LAYOUT

编号	尺寸 (MM)	
	A	B
YTC-A4250-02A	4.20	9.60
YTC-A4250-03A	8.40	13.80
YTC-A4250-04A	12.60	18.00
YTC-A4250-05A	16.80	22.20

	<b>深圳市怡远科技有限公司</b> SHENZHEN YIYUAN TECHNOLOGY CO., LTD		页码 (SHEET)	1/1	单位 (UNIT): MM
			版本 (REV)	A1	比例 (SCALE)
品名 (ITEM NO)		4.20间距单排直针 WAFER DIP TYPE	日期 (DATE)	2021. 10. 12	
料号 (PART NO)		YTC-A4250-**A	设计 (DESIGN)	LUO	
图号 (DWG NO)			审核 (CHECKED)	ROGER LI	GENERAL TOLERANCE X.±0.25 X.±2° .XX±0.20 .X±1° .XX±0.15 .XX±0.5° .XXX±0.10 .XXX±0.5°
			核准 (APPROVED)	ROC ZHAO	

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com