




| REV. | EC# | DESCRIPTION | DATE | DRAWN | CHECK | APPROVED |
|------|-----|-------------|-----------|-------|-------|----------|
| 1.00 | | 初版发行 | 2020-8-28 | 瞿寿坤 | 胡海萍 | 胡海萍 |
| | | | | | | |

| NUMBER OF PINS | DIM.A | DIM.B |
|----------------|-------|-------|
| 15P | 40 | 33.1 |
| 14P | 37.5 | 30.6 |
| 13P | 35 | 28.1 |
| 12P | 32.5 | 25.6 |
| 11P | 30 | 23.1 |
| 10P | 27.5 | 20.6 |
| 9P | 25 | 18.1 |
| 8P | 22.5 | 15.6 |
| 7P | 20 | 13.1 |
| 6P | 17.5 | 10.6 |
| 5P | 15 | 8.1 |
| 4P | 12.5 | 5.6 |
| 3P | 10 | 3.1 |
| 2P | 7.5 | 0 |



2PIN

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 3A



接触电阻: <= 0.01Ω

绝缘电阻: >= 1000MΩ

耐压: 1000V AC/minute

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。



PCB LAYOUT

| GENERAL TOLERANCES | | | |
|--------------------|-------|--------|--------|
| DIM | TOL | DIM | DEG |
| X | | X° | ±3.00° |
| X.X | ±0.35 | X.X° | ±2.00° |
| X.XX | ±0.25 | X.XX° | ±1.00° |
| X.XXX | ±0.15 | X.XXX° | |

| 2 | PIN | n PCS | 材质:黄铜,电镀:镀亮锡60u"MIN |
|-----|---------|-------|---------------------|
| 1 | Housing | 1 PCS | 材质:PA66颜色:本色 |
| NO. | NAME | QTY | DESCRIPTION |

深圳市虹成电子有限公司

| | | | | | | |
|------------------|-----|-----------|---------|-----------------------|------------|-------------|
| DRAW: | 瞿寿坤 | 2020-8-28 | TITLE: | WAFER 2. 5XHWA 卧式 DIP | DRAW NAME: | HCZZ0139-12 |
| DESIGN: | 瞿寿坤 | 2020-8-28 | SERIES: | 1501 SERIES | DRAW NO. | |
| CHECK: | 胡海萍 | 2020-8-28 | P/N: | | UNIT: | mm |
| APPROVED | 胡海萍 | 2020-8-28 | REV. | 1.00 | SCALE | N/A |
| CUSTOMER DRAWING | | | REV. | 1.00 | SCALE | N/A |
| | | | SHEET: | 1/1 | | |