







REV.	ECN. NO.	APPD.
A		

SPECIFICATIONS

Current Rating: 1A AC, DC
 Voltage Rating: 250V AC, DC
 Temperature Range: -25°C ~ +130°C
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Material
 Wafer: LCP UL94V-0
 PIN: C2680 Tin-plated
 Fixed piece: C2680 Tin-plated



PCB LAYOUT

X. ±0.30	X.° ±5°	UNITS mm	NAME/(INTENDED USE)	MINTRON CO.,LTD.
X ±0.20	X° ±2°	MATL		
.XX ±0.10	.XX° ±1°	FINISH	PART NO.(INTENDED USE)	TITLE:
.XXX ±0.05	.XXX° ±0.5°		Q'TY	
FLAT CABLE CONNECTOR			APPD: SUNNY	DWG. NO.:
			CHKD: LISA	MT20028-04A
			DR: ZOE 2023-06-16	SCALE 1/1
				SHEET 1/1
				REV. A