

Specifications:

规格:

Voltage rating: 125V AC/DC

额定电压: 125V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -45°C-+105°C

温度范围: -45°C-+105°C

Insulation resistance: ≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤10mΩ

接触电阻: ≤10mΩ

After environmental testing: ≤20mΩ

环境测试后: ≤20兆欧

X2009 T-PSN





- ① ② ③ ④

1. Series Number

2. Category: T-terminal

3. Material: P-Phosphor bronze

7. Plating style: SN-Bright Tin plating



X2009T-PSN	Phosphor Bronze	AWG#22-26	1.5mm(MAX)	Stamping Before plating:30u MIN Ni,70u Sn	X2009H
PART NO	Material	Wire Range	Insulation OD	Finish	Suitable XKB Terminal

广东星坤科技股份有限公司

生效	日期
文件	工程
MARK	REVISIONS
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn	

units:	mm
tolerance:	
X.X	±0.2mm
X.XX	±0.1mm
X.XXX	±0.05mm
UNSPECIFIED TOLERANCES	

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.: 2.00mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.: X2009T-PSN
APPD		DATE		SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO., LIMITED				SHEET 1/1	REVISION A0