


SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Housing Nylon66 UL94-V0

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-SPH-2x2Y	2.00	6.00
3	HC-SPH-2x3Y	4.00	8.00
4	HC-SPH-2x4Y	6.00	10.00
5	HC-SPH-2x5Y	8.00	12.00
6	HC-SPH-2x6Y	10.00	14.00
7	HC-SPH-2x7Y	12.00	16.00
8	HC-SPH-2x8Y	14.00	18.00
9	HC-SPH-2x9Y	16.00	20.00
10	HC-SPH-2x10Y	18.00	22.00
11	HC-SPH-2x11Y	20.00	24.00
12	HC-SPH-2x12Y	22.00	26.00

			GENREL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	SPH (2.0) 双排孔座	版本 REV.	A
			X.XX	±0.20	比 例 SCALE		产品料号 PART NO.	HC-SPH-2xNY	单 位 UNITS	mm
			X.XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
1	初版发行	日期	Angle	±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								