







SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated



Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-PHB-2x2ALT	2.00	9.00	3.00
3	HC-PHB-2x3ALT	4.00	11.00	3.00
4	HC-PHB-2x4ALT	6.00	13.00	3.00
5	HC-PHB-2x5ALT	8.00	15.00	5.00
6	HC-PHB-2x6ALT	10.00	17.00	7.00
7	HC-PHB-2x7ALT	12.00	19.00	9.00
8	HC-PHB-2x8ALT	14.00	21.00	11.00
9	HC-PHB-2x9ALT	16.00	23.00	13.00
10	HC-PHB-2x10ALT	18.00	25.00	15.00
11	HC-PHB-2x11ALT	20.00	27.00	17.00
12	HC-PHB-2x12ALT	22.00	29.00	19.00
13	HC-PHB-2x13ALT	24.00	31.00	21.00
14	HC-PHB-2x14ALT	26.00	33.00	23.00
18	HC-PHB-2x18ALT	34.00	41.00	31.00
20	HC-PHB-2x20ALT	38.00	45.00	35.00

			GENERL TOLERANCE		制图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	PHB (2.0) 双排立贴 (带双侧焊片)	版本 REV.	A
1			初版发行				产品料号 PART NO.	HC-PHB-2xNALT	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1