


SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Housing:Nylon66, UL94V-0



| Circuit | Part NO. | Dimensions mm | |
|---------|-----------|---------------|-------|
| | | A | B |
| 2 | HC-XA-2Y | 2.50 | 7.50 |
| 3 | HC-XA-3Y | 5.00 | 10.00 |
| 4 | HC-XA-4Y | 7.50 | 12.50 |
| 5 | HC-XA-5Y | 10.00 | 15.00 |
| 6 | HC-XA-6Y | 12.50 | 17.50 |
| 7 | HC-XA-7Y | 15.00 | 20.00 |
| 8 | HC-XA-8Y | 17.50 | 22.50 |
| 9 | HC-XA-9Y | 20.00 | 25.00 |
| 10 | HC-XA-10Y | 22.50 | 27.50 |
| 11 | HC-XA-11Y | 25.00 | 30.00 |
| 12 | HC-XA-12Y | 27.50 | 32.50 |
| 13 | HC-XA-13Y | 30.00 | 35.00 |
| 14 | HC-XA-14Y | 32.50 | 37.50 |
| 15 | HC-XA-15Y | 35.00 | 40.00 |
| 16 | HC-XA-16Y | 37.50 | 42.50 |

| | | | | | | | | |
|-----------|------------------------|-------------------|-------------------|------------------|----------------------------------------------------------|----------|-------------|-----|
| | | | GENERAL TOLERANCE | 制图 DRAWING | 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD | | | |
| | | | DIM TOL | 审核 CHECK | | | | |
| | | | X.X ±0.30 | 批准 APPROVAL | 产品名称 TITLE | 2.5 孔座 | 版本 REV. | A |
| 1 | 初版发行 | | X.XX ±0.20 | 比例 SCALE | 产品料号 PART NO. | HC-XA-NY | 单位 UNITS | mm |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | X.XXX ±0.10 | 投影 Projection | 材料 MATERIAL | | 页次 SHEET | 1/1 |
| | | | Angle ±3.0° | | | | | |