



| 标记<br>MARK. | 更改内容<br>MODIFICATION | 日期<br>DATE | 修改<br>DRAW | 核准<br>APPROVE |
|-------------|----------------------|------------|------------|---------------|
|             |                      |            |            |               |
|             |                      |            |            |               |

技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、额定电流 Current rating:3.0A AC,DC
- 3、额定电压 Voltage rating: 250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻 Insulation resistance:≥1000MΩ
- 7、耐压 Withstand voltage:1000V AC/minute
- 8、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| 线数<br>poles | 型号<br>Type  | 尺寸Dimensions mm |       |
|-------------|-------------|-----------------|-------|
|             |             | A               | B     |
| 2           | SH25027-2Y  | 2.50            | 5.80  |
| 3           | SH25027-3Y  | 5.00            | 8.30  |
| 4           | SH25027-4Y  | 7.50            | 10.80 |
| 5           | SH25027-5Y  | 10.00           | 13.30 |
| 6           | SH25027-6Y  | 12.50           | 15.80 |
| 7           | SH25027-7Y  | 15.00           | 18.30 |
| 8           | SH25027-8Y  | 17.50           | 20.80 |
| 9           | SH25027-9Y  | 20.00           | 23.30 |
| 10          | SH25027-10Y | 22.50           | 25.80 |
| 11          | SH25027-11Y | 25.00           | 28.30 |
| 12          | SH25027-12Y | 27.50           | 30.80 |
| 13          | SH25027-13Y | 30.00           | 33.30 |
| 14          | SH25027-14Y | 32.50           | 35.80 |
| 15          | SH25027-15Y | 35.00           | 38.30 |
| 16          | SH25027-16Y | 37.50           | 40.80 |
| 17          | SH25027-17Y | 40.00           | 43.30 |

| TOLERANCE UNLESS OTHERWISE SPECIFIED |             | *: Inspection Item                |  |
|--------------------------------------|-------------|-----------------------------------|--|
| .X±0.30                              | X.°±1°      | (NO) :Cp/Cpk and SPC Control Item |  兆星精密电子(深圳)有限公司 |
| .XX±0.20                             | .X°±        |                                   |  |
| .XXX±0.10                            | .XX°±       | 材料<br>MATERIAL                    | 名称<br>TITLE  |
| 制图<br>DRAWIN                         | 料厚<br>THICK | PA66                              | HA2.54胶壳-5Pin  |
| 审核<br>CHECKED                        | 料宽<br>WIDE  |                                   | 编号<br>DWG NO.  |
| 批准<br>APPROVE                        | 日期<br>DATE  |                                   | ZX-HA2.54-5PJk   |
|                                      |             |                                   | 单位<br>UNIT   |
|                                      |             |                                   | mm   |
|                                      |             |                                   | 比例<br>SCALE  |
|                                      |             |                                   | 1:1  |
|                                      |             |                                   | 版本<br>REV.   |
|                                      |             |                                   | A  |
|                                      |             |                                   | 角法<br>PROJ.  |
|                                      |             |                                   |                 |
|                                      |             |                                   | 规格书  |

