



CUSTOMER		CUSTOMER'S P/S	
ISSUE DATE	2023. 1. 16	OUR P/N	XRCD75-1R0M

### 1. 外观尺寸图 DIMENSIONS (mm)



### 2. 接线图 CONNECTION (BOTTOM VIEW)




### 3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	$\Phi 0.43$	5TS (REF)	CLOSED

### 4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz 0.25V	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD75-1R0M	$1.0\mu\text{H}\pm 30\%$	$0.02\ \Omega$	7.0A	1R0	—

### 5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. :  $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
陈泽伟	刘汉清		

2023. 1. 16	2023. 1. 16		
-------------	-------------	--	--

# 试产（样）报告

(TEST REPORT)

2/2

MODEL NO: 产品型号:	XRCD75-1R0M	EVALUATED Q' TY: 试样数:	10PCS
--------------------	-------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	SMD 7850	TESTED DATE: 试制日期:	2023.01.16
---------------------------	----------	-----------------------	------------

LOTS 序号	SPC 规格	1KHz/0.25V L(μH)	DCR(Ω)							
		1.0μH±30%	MAX 0.02 Ω							
1		1.21	0.012							
2		1.22	0.012							
3		1.18	0.012							
4		1.25	0.013							
5		1.23	0.013							
6		1.19	0.012							
7		1.20	0.012							
8		1.23	0.012							
9		1.25	0.013							
10		1.27	0.013							
11										
12										
13										
14										
15										

(DATA) 试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115  
 备注: 用200KHz 0.25V全检  
 外观: OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW	东莞市祥如电子有限公司
	陈泽伟 2023.01.16	