



电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk
 V : hooya89

皓宇电子
 HOUYA ELECTRONICS

Rating: 3A 125V AC
 Contact Resistance: 50m Ω Max
 Insulation Resistance: DC 500V 100m Ω Min
 Dielectric Strength: AC 1000V 1minute
 Total travel: 1.4 \pm 0.4mm
 Operating Force: 200 \pm 50gf
 Operating Life: 10,000 cycles
 Operating Temperature: 0 $^{\circ}$ C~85 $^{\circ}$ C
 Function: OFF-(ON)

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ± 0.1	ANGULAR						
				ABOVE 5mm: ± 0.2	$\pm 1^{\circ}$	NO	DATE	REVISIONS		BY	APPD
4	NUT	BRASS	1	Ni-Plating	TITLE: PUSH SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
3	TERMINAL	BRASS	2	Ag/Sn-Plating	MODEL: PB-11D02-N-B		SCALE: 1:1	CHK'D			
2	CAP	PBT	1		 HAOYU(HONG KONG)LIMITED 皓宇(香港)有限公司		APPD				
1	BASE	BRASS	1	Ni-Plating			PRO.AGL: 		REV :A0		
NO.	PART NAME	MATERIAL	QTY	FINISHING							