




3D VIEW



Specifications:

规格:
 Current rating:5A AC/DC
 额定电流: 5A AC/DC
 Voltage rating:500V AC
 额定电压: 500V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-55℃-+105℃
 温度范围: -55℃-+105℃
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT+30% GF UL 94V-0
 绝缘体: PBT+30% GF UL 94V-0
 SHELL: Steel Plated Ni
 外壳: 钢 镀镍
 CONTACT MATERIAL:Brass
 触点材料: 黄铜

X06 XX F T X X X

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No. Pin No:XX-15;26;44;62
- ③ Welding Board Angle :F-Female
- ④ T:Tradutional
- ⑤ Planting Cateogtry:1:1U' ;2:2U' ;3:3U' ;4:5U' ;5:15U' 6:30U' ;7: AuSn
- ⑥ B:Black W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图示				

NO.OF CONTACT	A	B	C	D	E	F
15	16.35	24.99	30.80	2.29	0.28	1.145
26	24.75	33.30	39.20	2.29	0.50	1.145
44	38.35	47.04	53.00	2.29	0.50	1.145
62	54.75	63.50	69.40	2.42	0.58	1.21

广东星坤科技股份有限公司
 文件工程章

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR ±5°
 L≤ 4 ±0.2
 4<L≤ 16 ±0.3
 16<L≤ 63 ±0.4
 L> 63 ±0.5

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	D-USB
CHKD	UNIT: mm/in	PART NO.: X06XXFTXXX
APPD	SIZE: A4	DWG NO.: X-X06XXFTXXX
		WEIGHT SHEET REVISION
		1/1 A0