




Specifications:  
 规格:  
 Voltage rating:30V AC/DC  
 额定电压: 30V AC/DC  
 Current rating:2A AC/DC  
 额定电流: 2A AC/DC  
 Withstanding voltage:500V AC/minute  
 耐受电压: 500V AC/分钟  
 Temperature range:-25°C~+85°C  
 温度范围: -25°C~+85°C  
 Insulation resistance:100MΩ  
 绝缘电阻: 100MΩ  
 Contact resistance:20mΩ Max  
 接触电阻: 20mΩ Max

X1300 T - P V01  
 ① ② ③ ④


- 1. Series No
- 2. Category:T-Terminal
- 3. Material:P-Phosphor Bronze
- 4. Plating:V01-Gold Flash



SECTION:A-A  
SCALE:1:1



SECTION:B-B  
SCALE:1:1



X1300T-PV01	Phosphor Bronze	AWG#30~26 O.D 0.98mm Max	X9635TF
PART NO	Material	Wire Range	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.3mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1300T-PV01
CHKD		UNIT: mm/in	DWG NO.: X-X1300T-PV01
APPD		SIZE: A4	



XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
DESCRIPTION					DATE	APPROVED
REVISIONS					DATE	APPROVED
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						