





RoHS





TOTAL HEIGHT	
CODE	H
A1	1.5
A2	1.7

PCB Layout (Pattern Side)



SHRAPNEL	
CODE	MATERIAL/QTY
D2	SUS/1PCS
D4	SUS/2PCS

OPERATING FORCE	
CODE	VIGOR
B2	180±30gf
B3	250±50gf



Ⓕ	Dust film	1	Polyimide tape		
Ⓖ	Terminal	2	Phosphor bronze	Silvering	
Ⓓ	Reed	2	SUS	Silvering covered	
Ⓒ	Base	1	LCP	White	
Ⓑ	Cover	1	SUS	Nickel plated	
Ⓐ	Button	1	LCP	Black	
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co, Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-1064SA-A□B□-D□
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified

angle	±2'
10~30	±0.30
5~10	±0.20
~ 5	±0.10