



SPECIFICATIONS

- 1、 Current Rating: 1A AC, DC
- 2、 Voltage Rating: 125V AC, DC
- 3、 Temperature Range: -25°C~+85°C
- 4、 Contact Resistance: 20mΩ Max
- 5、 Insulation Resistance: 100MΩ Min
- 6、 Withstanding Voltage: 500V AC/minute
- 7、 Material: Phosphoric bronze Tin-plated
- 8、 Applicable Wire Sizes: AWG#28~32#



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/8/18	X1251-T-PN	
CHECKED			SCALE: 1:1	
APPROVALS			SHEET 1 OF 1	
TOLERANCES ARE		ANGLE	PROJ.	
30 ^{±0.15}	±0.30	±2°	PROJ.	
10 ^{±0.10}	±0.20			
5 ^{±0.05}	±0.10			

DEALON 德之隆
ELECTRONICS CO.,LTD

1.25mm Crimp Style Connectors