

- SPECIFICATIONS**
1. Current Rating: 1A AC, DC
  2. Voltage Rating: 50V AC, DC
  3. Temperature Range: -25°C~+85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 100MΩ Min
  6. Withstanding Voltage: 500V AC/minute
  7. Material: Phosphoric bronze Tin-plated
  8. Applicable Wire Sizes: AWG#26~32#

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|         | A    |       | NEW          |         |        |        |

|                |          |           |                                    |             |            |        |        |
|----------------|----------|-----------|------------------------------------|-------------|------------|--------|--------|
| APPROVALS      |          | DATE      | TITLE:                             |             | PART NO.   | SCALE: | SHEET  |
| DRAWN          | G.M.Chen | 2014/8/18 | EDELON 德之隆®<br>ELECTRONICS CO.,LTD |             | X1253-T-PN | 1:1    | 1 OF 1 |
| CHECKED        |          |           |                                    |             |            |        |        |
| APPROVALS      |          |           |                                    |             |            |        |        |
| TOLERANCES ARE |          | ANGLE     | UNIT:                              | DRAWING NO. |            |        | PROJ.  |
| ±0.10          | ±0.20    | ±2°       | mm                                 |             |            |        |        |
| ±0.15          | ±0.10    |           |                                    |             |            |        |        |
| ±0.10          |          |           |                                    |             |            |        |        |

