



技术要求:

1. 标识清晰可见, 表面不得有划痕、裂纹、变形、起泡、污垢, 毛刺等明显影响使用功能和接触性能的缺陷;
2. 材料: 磷铜, 厚度0.2mm;
3. 表面处理: 镀锡;
4. 额定功率: 250V.AC/DC 3A;
5. 温度范围: -25~+85℃;
6. 接触电阻: $\leq 0.02\Omega$;
7. 绝缘电阻: $\geq 1000M\Omega$;
8. 耐压: 1000V AC/1min;
9. 适用线规: WAG28#~22#。

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/8/18	ELECTRONICS CO.,LTD	
CHECKED			TITLE: 2.00mm Crimp Style Connectors	
APPROVALS			PART NO.	X2006-T-PN
TOLERANCES ARE			UNIT: mm	SCALE: 1:1
30 ^{±0.15}	±0.30	ANGLE		SHEET 1 OF 1
10 ^{±0.10}	±0.20			PROJ.
5 ^{±0.10}	±0.15	±2'	DRAWING NO.	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	